



Inspiración Profesional

Lavamanos especializado para zonas con alto tránsito.

- Superficie autodrenante que evita empozamientos.
- Amplio pozo.
- Apto para personas con movilidad reducida al ser instalado según medidas recomendadas.
- Disponible en un agujero.

Professional Inspiration

Special handwashers for high traffic areas.

- Self-draining surface that prevents deposits.
- Large depth.
- Suitable for disabled people to be installed according by recommended measures.
- Available in a hole.

SERIE PROFESIONAL

AMPLIUX

Lavamanos de colgar
Wall hung lavatory

Spec. Sheet

Lavamanos / Lavatory

Technical Information

Material	Porcelana sanitaria
Material	Vitreous China

Dimensiones (An x L x Al)	539 x 559 x 402.2 mm.
Dimensions (W x H x D)	21.2 x 22 x 15.8 inch.

Dimensiones del pozo (An x Pr) 395 x 350 mm.
Basin dimensions (W x D) 15.5 x 13.7 inch.

Profundidad de pozo	127 mm.
Basin depth	5 inch.

Ubicación rebose	Pared trasera
Overflow location	Rear wall

Diámetro desagüe
Drain diameter

Ø44 mm.

Peso Neto (aprox.)	16.3 kg.
Net Weight (approx.)	35.9 lb.

Altura de instalación	864 mm.
Installation height	34 inch.

Tipo de griferías compatibles	Monocontrol
Compatible faucets kind	Single lever



*Further information refer to warranty and return conditions.

Color Blanco .020
Color  White .020

postventa@incesastd.com
www.americanstandard-la.com

Care and cleaning

- Para la limpieza, utilice un detergente suave como jabón líquido de PH neutro y agua tibia.
- No utilice limpiadores abrasivos que puedan rayar u opacar la superficie.
- No use limpiadores que contengan CLORO, este químico puede causarle daños a la pieza.
- Siempre pruebe la solución de limpieza en un área oculta antes de aplicarla a toda la superficie.
- Limpie con un trapo y enjuague completa e inmediatamente con agua después de aplicar limpiadores.
- Enjuague y seque las superficies cercanas que se hayan rociado.

- For best cleaning results use a mild soap with neutral PH and warm water.
- Do not use abrasive cleaners since they might scratch the surface.
- Do not clean the product with CHLORINE'S substances will cause damage on the piece.
- Always test cleaning products on a small hidden area before applying it to the entire product.
- After using cleaners, rinse the surface using water and dry with a cloth.

Technical Drawing

VISTA SUPERIOR

Pared terminada

197

152

539

Desagüe
Ø44


83

29

Agujeros para brazo soporte

Agujeros para brazo soporte

VISTA FRONTAL



Unidades / Units: mm.

Estas dimensiones son nominales y son sujetas a cambio sin previo aviso.
These dimensions are nominal and are subject to change without prior notice.

Related products

- Include semipedestal.
- Includes semi-pedestal.
- Ref. 19.00357 Soporte Zurn 1231 (pared liviana)
- Ref. 19.00357 Support Zurn 1231 (light wall)
- Ref. 19.00354 Soporte Zurn 1251 (pared concreto)
- Ref. 19.00354 Support Zurn 1251 (concrete wall)
- Ref. 19.06367 Soporte con brazos ajustables Zurn 1253 (pared concreto)
- Ref. 19.06367 Support with adjustable arms Zurn 1253 (concrete wall)

AMERICAN STANDARD